



Color: ■ gray

Technical data		
Number of spacings		2 -times
Electrical data		
Rated current		125 A
Physical data		
Width		29.1 mm / 1.146 inches
Material data		
Color		gray
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.05 MJ
Weight		15.1 g
Commercial data		
PU (SPU)		100 (25) pcs
Packaging type		Box
Country of origin		IN
GTIN		4045454074524
Customs tariff number		85366990990



Product Classification	
UNSPSC	39121410
eCl@ss 10.0	27-14-11-40
eCl@ss 9.0	27-14-11-40
ETIM 9.0	EC000489
ETIM 10.0	EC000489
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 284-412

↓

Documentation				
Bid Text				
284-412	19.02.2019	xml 2.58 KB	↓	
284-412	19.09.2017	doc 22.50 KB	↓	


CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 284-412	EPLAN Data Portal 284-412
	WSCAD Universe 284-412
	ZUKEN Portal 284-412

Installation Notes

Commoning



Commoning with comb-style jumper bar.
Individual arrangement: 125 A
Two jumpers combined in one clamping unit: 100 A



Connecting 35 mm² (2 AWG) conductors to commoned terminal blocks.
Screw clamp connection, side-entry wiring

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com