







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210686	2021/05/12	Vicky	△B X4

Recommended
Panel Cut-Out△B
M8S-XXPMMR-SF8001


XX: No. Of Pin



PCB Layout



Pin Assignments Front View



- △B Note:
- * RoHS Compliant
 - * Ⓢ Important dimension
 - * Waterproof rate: IPX8, unmated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - * Shield: Metal
 - * Ground: Metal
 - * Nut: Metal
 - * O-Ring: Rubber, Green
 - * For panel thickness: 2.0~4.0mm
 - * For pcb thickness max: 1.6mm
 - * Nut is packed separately in pe bag

UNIT: mm		 	TITLE N SEN, M8-SHLD, SCREW RECEPTACLE, M, M, PCB R			
TOLERANCE			SCALE	SIZE	SHEET	OF
.X ±0.25			2:1	A4	1	1
.XX ±0.1						
.XXX ±0.05						
ANGLES ±1°			REV. B	WC-REV. A.7	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Yulong_wang	2016-01-20
DWG NO	CHECKED BY	DATE
M8S-XXPMMR-SF8001	Cary	2016-01-20
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2016-01-20