


Data Sheet | Item Number: 890-502/342-000

Strain relief housing; 2-pole; with locking clip; for 1 cable; 3.8 ... 8.2 mm; 17.5 mm; black

<https://www.wago.com/890-502/342-000>



Color: ■ black



Dimensions in mm

Strain relief housing *WINSTA*® MINI 2-pole

The strain relief housing from the *WINSTA*® MINI product line is the best solution for reliable installation. You can rely on the level of quality of *WINSTA*® components from WAGO for your electrical installation accessories too. *WINSTA*® MINI satisfies the demand for miniaturisation. Our smallest pluggable connection system is primarily suited for lights, for instance, since as a result of LED technology; due to complex systems, these offer significantly less space for the connection technology. The strip length is 17.5 mm.

Lower costs through fast commissioning and elimination of service expenses – solutions from *WINSTA*® MINI

WINSTA® is the pluggable connection system that is optimally tailored to the strict requirements of electrical installation. It ensures error-free installation of cables and components, quickly and reliably. Now you can also lower installation costs without compromising safety and quality: with protection against mismatching eliminates the need for servicing and prevents unnecessary downtime.

- consistent IP40 protection
- convenient installation and commissioning

Notes	
General safety information	NOTICE: Observe installation and safety instructions! 1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100). 2. Do not install while energized or under load. 3. Use only for its intended purpose. 4. Observe applicable national regulations, standards and directives. 5. Observe the technical specifications of the products. 6. Ensure correct polarity assignment. 7. Do not use damaged or contaminated components. 8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters. 9. Insert conductors up to the stop. 10. Use only with locking lever and strain relief. 11. Use original accessories only. To be sold only with installation instructions!

Connection Data	
Connection 1	
Pole number	2
Connectable sheathed cable diameter	3.8 ... 8.2 mm
Strip length (outer insulation)	17.5 mm

Physical data	
Pin spacing	4.4 mm / 0.173 inches
Width	15.6 mm / 0.614 inches
Height	13.2 mm / 0.52 inches
Depth	29.7 mm / 1.169 inches

Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Insulation material (main housing)	Polyamide (PA66)
Fire load	0.057 MJ
Weight	2.1 g

Environmental requirements	
Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data	
PU (SPU)	50 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821765554
Customs tariff number	39269097900



Product Classification	
UNSPSC	39121722
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
890-502/342-000

↓

Documentation			
Bid Text			
890-502/342-000	19.02.2019	xml 2.85 KB	↓
890-502/342-000	03.12.2014	doc 23.50 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 890-502/342-000	WSCAD Universe 890-502/342-000
↓	↓
	ZUKEN Portal 890-502/342-000
	↓