



Emergency Stop FF01 Series FF01-26BBREYG3



*The photo is a sample image.
 The color and shape may differ from the actual product.
 *Please be sure to check the actual color and shape with a product sample.

3D CAD

PDF

Product Introduction

Compact Emergency Stop Push Button Switch (FF01 Series) - Solder Terminal Type - 2-Pole Single Throw - No Arrow Indicator - Φ30 - Function: Lock Type (Push Lock, Pull or Turn Reset) - Panel Seal Mechanism - IP65 - UL/TUV Certified - Operating Temperature Range: -25 to 60° C - Applications: Small Wireless Control Panels, Teaching Pendants, Portable Devices, Handheld Devices - EU-RoHS Compliant - Model Number: FF01-26BBREYG3

Product overview

Model Name	FF01-26BBREYG3
category	emergency stop
series	FF01
Subcategory	Non-illuminated switch
Current capacity for detailed display1	0.5A DC24V
Operating temperature range (° C)	-25/+60
Number of poles	2 poles
Function 1	ON-OFF
Function 2	rock
Operation part shape	30
Terminal shape	Solder terminals
Environmental performance	RoHS

Functionality-enhancing accessories

- ▶ Jig AT-119
- ▶ Switchguard AT-220 (Switchguard - Yellow)
- ▶ Nameplate AT-221 (Nameplate - Yellow)
- ▶ Nameplate AT-222 (Nameplate - Yellow)
- ▶ Nameplate AT-223 (Nameplate - Yellow)
- ▶ Nameplate AT-224 (Nameplate - Yellow)

Total 6 items

Back to Series TOP