


all categories > through hole > th series insert / spacer > threaded spacer



>> request quote / information | >> download specs

Threaded Spacer

- This Spacer is mounted on PCB by inserting into through-hole. Screws can be inserted both from component and from solder side. Taping type has adsorption seal for vacuum pick. It needs to be removed after reflow.
- Adaptive PCB Thickness....1.6t and over (other PCB thickness applicable)
* Mounter should have automatic recognition system
- Current Capacity....
TH-1.6-□-M2□□□20A
TH-1.6-□-M2.6□□ 20A
TH-1.6-□-M3□□□30A
- Dimensions....
M2 P=0.4
M2.6 P=0.45
M3 P=0.5
- Finish....Sn plating over Ni
- Material....Brass
- Recommended Metal Mask Thickness....150~200μm
- Tightening Torque....
TH-1.6-□-M2□□□ 1.5kgf-cm(14.7N-cm) and below
TH-1.6-□-M2.6□□ 3kgf-cm(29.4N-cm) and below
TH-1.6-□-M3□□□ 5kgf-cm(49N-cm) and below (X-direction)
3kgf-cm(29.4N-cm) and below (Y-direction)

- Save To Favorites
- Download Catalog

[Ask a Question](#)

[Pre-Production Quote Request](#)

[Request Sample](#)




ADD TO CART

N/O	A	B	H	M	Package
TH-1.6-0.5-M2	4.0	2.5	0.5	M2	450
TH-1.6-1.0-M2	4.0	2.5	1.0	M2	450
TH-1.6-1.5-M2	4.0	2.5	1.5	M2	450
TH-1.6-2.0-M2	4.0	2.5	2.0	M2	450
TH-1.6-2.5-M2	4.0	2.5	2.5	M2	350
TH-1.6-3.0-M2	4.0	2.5	3.0	M2	350
TH-1.6-3.5-M2	4.0	2.5	3.5	M2	350
TH-1.6-4.0-M2	4.0	2.5	4.0	M2	250
TH-1.6-4.5-M2	4.0	2.5	4.5	M2	250
TH-1.6-5.0-M2	4.0	2.5	5.0	M2	250
TH-1.6-0.5-M2.6	4.5	3.1	0.5	M2.6	450
TH-1.6-1.0-M2.6	4.5	3.1	1.0	M2.6	450
TH-1.6-1.5-M2.6	4.5	3.1	1.5	M2.6	450
TH-1.6-2.0-M2.6	4.5	3.1	2.0	M2.6	450
TH-1.6-2.5-M2.6	4.5	3.1	2.5	M2.6	350
TH-1.6-3.0-M2.6	4.5	3.1	3.0	M2.6	350
TH-1.6-3.5-M2.6	4.5	3.1	3.5	M2.6	350
TH-1.6-4.0-M2.6	4.5	3.1	4.0	M2.6	250
TH-1.6-4.5-M2.6	4.5	3.1	4.5	M2.6	250
TH-1.6-5.0-M2.6	4.5	3.1	5.0	M2.6	250
TH-1.6-5.5-M2.6	4.5	3.1	5.5	M2.6	350
TH-1.6-6.0-M2.6	4.5	3.1	6.0	M2.6	350
TH-1.6-6.5-M2.6	4.5	3.1	6.5	M2.6	300
TH-1.6-7.0-M2.6	4.5	3.1	7.0	M2.6	300
TH-1.6-7.5-M2.6	4.5	3.1	7.5	M2.6	300
TH-1.6-8.0-M2.6	4.5	3.1	8.0	M2.6	300
TH-1.6-0.5-M3	5.0	3.5	0.5	M3	450
TH-1.6-1.0-M3	5.0	3.5	1.0	M3	450
TH-1.6-1.5-M3	5.0	3.5	1.5	M3	450
TH-1.6-2.0-M3	5.0	3.5	2.0	M3	450
TH-1.6-2.5-M3	5.0	3.5	2.5	M3	350
TH-1.6-3.0-M3	5.0	3.5	3.0	M3	350
TH-1.6-3.5-M3	5.0	3.5	3.5	M3	350
TH-1.6-4.0-M3	5.0	3.5	4.0	M3	250
TH-1.6-4.5-M3	5.0	3.5	4.5	M3	250
TH-1.6-5.0-M3	5.0	3.5	5.0	M3	250
TH-1.6-5.5-M3	5.0	3.5	5.5	M3	350
TH-1.6-6.0-M3	5.0	3.5	6.0	M3	350
TH-1.6-6.5-M3	5.0	3.5	6.5	M3	300
TH-1.6-7.0-M3	5.0	3.5	7.0	M3	300
TH-1.6-7.5-M3	5.0	3.5	7.5	M3	300
TH-1.6-8.0-M3	5.0	3.5	8.0	M3	300
TH-1.6-8.5-M3	5.0	3.5	8.5	M3	250
TH-1.6-9.0-M3	5.0	3.5	9.0	M3	250
TH-1.6-9.5-M3	5.0	3.5	9.5	M3	250
TH-1.6-10-M3	5.0	3.5	10	M3	250

※ For Throgh Hole PCB only
You can order bulk type (no adsorption seal)
TH-1.6-0.5-M2-B
add -B for bulk type (100/package)

N/O	C	D
TH-1.6-M2	2.7	5.0
TH-1.6-M2.6	3.3	5.5
TH-1.6-M3	3.7	6.0

N/O	C	D
TH-1.6-M2	2.7	5.0
TH-1.6-M2.6	3.3	5.5
TH-1.6-M3	3.7	6.0



[Pre-Production Quote Request](#)