

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	46.96[CFM]
Max. Air Flow:	1.33[m ³ per min]
Max. Static Pressure:	0.201[In H ₂ O]
Max. Static Pressure:	50[Pa]
Fan Speed:	3500[RPM]
Noise:	34[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.24[A]
Input Power:	2.88[W]
Mass:	80[g]
IP Rating:	Potting not available
Tach / Locked Rotor Output:	No
Status:	Active

PWM Speed Control Fans