

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [Ceres](#) / [Middle Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[Accessory](#)[Large Size](#)[Macro Size](#)[Middle Size](#)[Mini Size](#)[Others \(GBD\)](#)[Others \(MAB\)](#)[Others \(PLD\)](#)[Standard Size](#)[X-Lok](#) >[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 8888](#) >

ABOUT AMPHENOL LTW

[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

CB-04PMFP-LC7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977

You must login first to view the price

Quantity

- 1 +

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



Ceres, Middle Size,...
1CB-04BFMM-LL6A01
-20°C ~ +80°C



Ceres, Middle Size,...
1CB-04BFMM-LL6A02
-20°C ~ +80°C



Ceres, Middle Size,...
1CB-04BFMM-LL6A03
-20°C ~ +80°C



Ceres, Middle Size,...
1CB-04BFMM-LL6A04
-20°C ~ +80°C

Add to Cart

Inquiry

Specifications

Download / CAD

Nominal Current
10A

Connector Type
Receptacle

Shielded
Plastic, Non-shielded

No. of Contacts
04

Connector Gender
Male

Backshell
Circular

Mating Style
2 Points Lock

IP Rating
IPX7

Assembly Style
PCB 180°

[More Options](#)

People Also Bought

