

# Hasps

BradyID.com/lockouttagout



## Steel Group Lockout Hasps

- Constructed of vinyl-coated high tensile steel w/ rust resistant plating
- Lock holes: 3/8" diameter

| Catalog # | Description          | Qty. |
|-----------|----------------------|------|
| 133161    | 1" Diameter Jaws     | 1    |
| 65375     | 1" Diameter Jaws     | 12   |
| 133162    | 1-1/2" Diameter Jaws | 1    |
| 65376     | 1-1/2" Diameter Jaws | 12   |



## Steel Group Lockout Hasps with Tabs

- Tamperproof interlocking tabs prevent unauthorized opening
- Case-hardened steel with rust proof plating and bright red vinyl insulation
- Lock holes: 3/8" diameter

| Catalog # | Description          | Qty. |
|-----------|----------------------|------|
| 105718    | 1" Diameter Jaws     | 1    |
| 105719    | 1-1/2" Diameter Jaws | 1    |



## Corrosion-Resistant Group Lockout Hasps

- 12 gauge epoxy coated steel provides superior rust resistance and added dielectric strength
- Lock holes: 5/16" diameter

| Catalog # | Description      | Qty. |
|-----------|------------------|------|
| T218      | 1" diameter jaws | 1    |
| T220      | 1-1/2" diameter  | 1    |



## Aluminum Economy Group Lockout Hasps

- Non-sparking, aluminum small hasps are a great addition to your tool box
- Lightweight at only 1-1/2 ounces
- Lock holes: 3/8" diameter

| Catalog # | Description          | Qty. |
|-----------|----------------------|------|
| 105720    | 1" Diameter Jaws     | 1    |
| 105721    | 1-1/2" Diameter Jaws | 1    |



## Non-Conductive Group Lockout Hasps

- Strong, rigid plastic resin
- Excellent electrical insulating
- Performs at low temps, excellent heat resistance
- Patent #7,124,606

| Catalog # | Description      | Qty. |
|-----------|------------------|------|
| LH220A    | Red Lockout Hasp | 1    |



## Heavy Duty Lockout Hasp

- Hasp allows multiple workers to lockout at each isolation point
- Stainless steel construction
- Accommodates up to 1/3" dia. padlock shackles

| Catalog # | Description     | Qty. |
|-----------|-----------------|------|
| 871239    | Heavy Duty Hasp | 24   |



## Dual Jaw Hasp

- Dual construction allows for increased versatility in a single product
- Larger jaw measures 1.25" x 1.75"
- Smaller jaw measures 0.75" dia.

| Catalog # | Description   | Qty. |
|-----------|---------------|------|
| 236919    | Dual Jaw Hasp | 1    |



## Non-Conductive Nylon Group Lockout Hasp

- Accommodate up to 6 locks
- Withstands up to 1,000 lbs despite weighing only 1 oz.
- Dimensions: 7"H x 1-3/4"W
- Lock holes: 3/8" diameter

| Catalog # | Description        | Qty. |
|-----------|--------------------|------|
| 99668     | Nylon Lockout Hasp | 1    |



## Labeled Group Lockout Hasps

- Tough 5052 anodized aluminum alloy hasps include tamperproof locking tabs
- Write-on label accepts pencil, pen or marker. Pen and pencil markings are easily erased for repeated use
- Dimensions: 7-1/4"H x 3"W x 3/16"D
- Lock holes: 5/16" dia.



Legend Option 1

| Catalog # | Color  | Qty. |
|-----------|--------|------|
| 65960     | Red    | 5    |
| 65961     | Silver | 5    |
| 65962     | Blue   | 5    |
| 65963     | Green  | 5    |
| 65964     | Gold   | 5    |
| 65967     | Combo* | 5    |



Legend Option 2

| Catalog # | Color  | Qty. |
|-----------|--------|------|
| 65970     | Red    | 5    |
| 65971     | Silver | 5    |
| 65972     | Blue   | 5    |
| 65973     | Green  | 5    |
| 65974     | Gold   | 5    |
| 65975     | Combo* | 5    |



Legend Option 3

| Catalog # | Color | Qty. |
|-----------|-------|------|
| 39480     | Red   | 5    |

\*Combo includes 1 each of the five colors listed above.