

232EC6

Industrial Connector

2CMA102031R1000



Industrial Connectors, 2P+E, 32A, 200 ... 250 V Clock
Position Of Grounding Contact 6 hour Color code Blue

GENERAL

Product Name	Industrial Connector
Product ID	2CMA102031R1000
Function	Connector
EAN	739269312
Catalog Description	Industrial Connectors, 2P+E, 32A, 200 ... 250 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420089
E-Number Norway	1540704
E-Number Sweden	E2416185
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EC
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...6 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	79 millimetre
Product Net Height	93 millimetre
Product Net Length	182 millimetre
Product Net Depth	182 millimetre
Product Net Weight	0.26 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.6 kilogram
Package Length	182 millimetre
Package Units	box 10 piece