

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

XN4E-TL403Q4MR 30mm Emergency-Stop Lighted



Add to Cart

Key Features

- Available in plastic bezel, metallic padlock, flush bezel
- Only 47.7mm depth behind the panel for up to 4 contacts (XN1E)
- Unique "Safe Break Action"
- Direct Opening Action (IEC60947-5-5, 5.2, IEC60947-5-1, Annex-K)
- Safety Lock mechanism (IEC60947-5-5, 6.2)
- Push-to-lock, pull/turn-to reset built into one switch(XN1E and XN5E); Push-to-lock, turn to reset (XN4E)
- RoHS compliant, lead free design, UL-listed, cUL, TUV, CE



Specifications

Literature

Downloads

Product Type	Emergency-Stop Illuminated
Operation Type	Turn
Mounting Hole Size	Φ30mm
Color	Red
Normally Open Contacts	0
Normally Closed Contacts	3
Illumination Voltage	24V AC 24V DC