



Part Number : [191610334](#)
Product Description : Splash Proof Snap Receptacle
Insulator, Carton
Series Number : 19161
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : SPR-1



Documents and Resources

Drawings

[191610334 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19161
Description	Splash Proof Snap Receptacle Insulator, Carton
Product Name	Splash Proof
Style	Splash Proof
Type	Snap Receptacle
UPC	800753112049

Electrical

Voltage - Maximum	N/A
-------------------	-----

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	PVC
Lock to Mating Part	No
Net Weight	1.037/g
Orientation	Straight
Packaging Type	Carton
Tab Thickness	N/A

Tab Width	N/A
Wire Insulation Diameter	N/A
Wire Size (AWG)	14, 16, 18, 20, 22

This document was generated on Apr 23, 2026