








CONTACT DETAIL
(5/1)



PANEL CUT DIMENSION
(REFERENCE)

Discrete Wire Housing

Cohesion Cable Housing

PCR-E () PMD	#30AWG (7/0.1) Cohesion Cable	PMD
PCR-E () PMC	#28AWG (7/0.127) #30AWG (1/0.254) Cohesion Cable	PMC
PCR-E () PMB	#30AWG (7/0.1) Discrete Wire Housing 00.5~00.65	PMB
PCR-E () PMA	#28AWG (7/0.127) #30AWG (1/0.254) Discrete Wire Housing 00.5~00.65	PMA
PCR-E () PM	#28AWG (7/0.127) #30AWG (1/0.254) Discrete Wire Housing 00.8~01.0	PM
PART No.	Applicable Wire Size	WIRE SIZE MARK

TABLE 1

PART NO.	A	B	C	D	E	F	G	H	N	C/T NO. MARK
PCR-E20PM ()	33.40	27.40	13.20	11.43	16.45	21.60	21.65	23.8	20	1, 10, 11, 20
PCR-E28PM ()	38.48	32.48	18.28	16.51	21.53	26.68	26.7	28.9	28	1, 14, 15, 28
PCR-E36PM ()	43.56	37.56	23.36	21.59	26.61	31.76	31.8	34.0	36	1, 18, 19, 36
PCR-E50PM ()	52.45	46.45	32.25	30.48	35.50	40.65	40.7	42.9	50	1, 25, 26, 50
PCR-E68PM ()	63.88	57.88	43.68	41.91	46.93	52.08	52.1	54.6	68	1, 34, 35, 68
PCR-E96PM ()	81.66	75.66	61.46	59.69	64.71	69.86	69.9	72.1	96	1, 48, 49, 96

					5	CABLE HOUSING	PBT (GF)	2	_____	UL94V-0 BLACK	
					4	SPEACER	PBT (GF)	2	_____	UL94V-0 BLACK	
△					3	CONTACT	PHOSPHOR BRONZE	N	CONTACT AREA GOLD PLATING	TERMINAL AREA GOLD PLATING	
△					2	INSULATOR	PBT (GF)	1	_____	UL94V-0 BLACK	
△	Aug. 6 2019	T. M	Revise		1	SHELL	ZINC DIE CASTING	1	Ni PLATING	_____	
L.T.R.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE	
DATE		SCALE		UNIT		HTK HONDA TSUSHIN KOGYO CO., LTD.					
JUL. 07. 1998		2/1		mm (INCH)							3RD. A. P
APP. DATE&REV.											
DR.		DE.		CHK.		CHK.		APP.		NAME	1.27mm SPACING MALE CONNECTOR FOR PANEL MOUNT TYPE
T. MASUNO		T. MASUNO		S. YOSHIDA		_____		Y. KATO		PART NO.	PCR-E () PM ()
										REV.	1