

Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >

- [Middle Size](#)
- [Large Size](#)
- [ODVA](#)
- [Accessory](#)

- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >




RCP-5SPFFG-TCU7B10

Operating Temperature: -20°C ~ +80°C
Transmission Speed: Cat 5e
Shielded: Plastic, Shielded
Jacket Material: PVC
Certificate: N/A

You must login first for view the price

Quantity - 1 +

[Add to Cart](#) [Inquiry](#) 

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type ▼ [Search](#)

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

☐

☐

☐

☐

☐

☐

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle With Cable
Shielded Plastic, Shielded	No. of Contacts N/A
Connector Gender Jack	Backshell Circular
Mating Style 3 Points Lock	IP Rating IP67
Assembly Style PCB Board to Plug with Ground	
More Options	

People Also Bought

- 

RCP-5SPFFG-TCU7B10
- 

BBD-06AFMM-...
- 

AD-02AMMM-LL6A04
- 

CD-09AMFM-RL7A02
- 

ABD-04AFMM-SL7A10