

Home

About ALTW

Products

Supports

News & Events

Where to buy

Contact Us

Product Line

ZConnect

Ceres Connectors

X-Lok Connectors

M Series Sensor Connectors

> MPronto-12

> M8

> M10.5

> M12

> M20

> M23

> Distribution Box

> Guided M8

FLOS & FLOS+ Connectors

Power Connectors

RBL Connectors

HS-Lok Connectors

NMEA 2000 Connectors

RJ Connectors

USB Connectors

D-SUB Connectors

SSL Solution Connectors

HDMI Connectors

DVI Connectors

Fiber Optic Connectors

Cable Joiner

FICX Connectors

Cable Gland - Anti-UV

Vent

LED Indicator

CNC Products

Product Applications

Product Search

Home > Product Line > M Series Sensor Connectors > M12

Bookmark

Share

Print

Part Number : M12A-03BFFA-SL8001

Pin : Copper Alloy,Gold Plated

Connector Body : Thermoplastic, UL Recognized.;Zn Alloy ,Nickel Plated

Temperature Range : -40°C~+105°C

Download:

Sample 3D model(.stp)

Sample 3D model(.igs)

Add to inquiry list

Check inquiry list

Submit inquiry

Description	Details
Connector	M12 A Code
Connector Gender	Female connector
Mating Style	Screw Thread
Current Rating	4A
No. of Contacts	3 pins
Contact Gender	Female pin
Field installable	Field Installable (Solder)
Connector body type	Without strain relief
Backshell	Straight
Waterproof Rating	IP68
Cable OD Φ	4.5~6.5
Voltage rating	250V AC/DC

* Design and specifications are subject to change without notice.

update: 2021-03-02 00:00:00

Home

Industrial Automation

LED

Marine

Broadband Wireless Access

Renewable Energy

Smart Grids / Advanced Metering Infrastructure (AMI)

Terms of use

Privacy Policy

YouTube

LinkedIn

Amphenol LTW[®]
Unlimited InterConnects for Harsh Environments

Copyright © 2017 Amphenol LTW TECHNOLOGY CO., LTD. All Rights Reserved.
ADD: 5F-3, No.51, Sec.4, Zhongyang Rd., Tucheng Dist., New Taipei City 236, Taiwan Tel: +886-2-7741-6888
E-mail: sales@ltw-tech.com
Design by TSG Web