


SPECIFICATIONS:

METALIZED PLASTIC:

MATERIAL: HIGH TEMPERATURE ABS
PLATING: NICKEL OVER COPPER

PLASTIC:

MATERIAL: HIGH TEMPERATURE ABS
COLOR: BLACK
OPERATING TEMPERATURE: -55°C TO +125°C



BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS
(RECOMMENDED TORQUE 26 IN-OZ)
- (1) METAL STRAIN RELIEF CLAMP
- (2) STRAIN RELIEF SCREWS
(RECOMMENDED TORQUE 30 IN-OZ)

DIMENSIONS					
SIZE	A	B	C	D	E
009	31.50	24.99	31.01	15.19	8.51
015	40.01	33.32	35.00	15.19	8.51
025	53.49	47.04	38.00	15.19	11.00
037	70.00	63.50	40.01	15.19	11.00
050	67.49	61.00	40.01	18.21	11.99

973-YYY-YYYRYY1

SERIES _____
POSITIONS _____
009
015
025
037
050
MATERIAL _____
010 = PLASTIC
020 = METALIZED PLASTIC
COLOR _____
01 = BLACK (ONLY FOR 010 OPTION ABOVE)
12 = NICKEL OVER COPPER (ONLY FOR 020 OPTION ABOVE)
PUT-UPS _____
1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
07/15/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
1 1

REV
2

DWG NO.

973-YYY-0Y0RYY1