

TACT Switch™ Surface Mount Type

6.0X5.9mm Low Contact Resistance (Surface Mount)

SKPM Series

Long-stroke, soft-feel type with a 1.3mm travel, featuring metal contacts for low contact resistance.



Automotive

- Series type: Soft feeling type
- Absolute Maximum Ratings: 50mA 16V DC
- Rating (min.): 10μA 1V DC

Applications: Audio_TV: Pro audio
Automotive: Navigation/audio systems, HVAC,
Overhead consoles, Steering, Shifter

■ Product List

Products No.	Operating direction	Operating force (N)	Travel (mm)	Operating life (cycles)	Initial contact resistance	Dimensions (W×D×H) (mm)	Water-proof	Dust-proof	Automotive	Drawing No.
SKPMAME010	Top push	1.57	1.3	100,000	100mΩ max.	5.9×6.0×5.0	—	—	●	1
SKPMANE010	Top push	1.96	1.3	100,000	100mΩ max.	5.9×6.0×5.0	—	—	●	
SKPMAPE010	Top push	2.45	1.3	100,000	100mΩ max.	5.9×6.0×5.0	—	—	●	
SKPMBHE010	Top push	3.0	1.3	100,000	100mΩ max.	5.9×6.0×5.0	—	—	●	


⚠ Note

1. This catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
2. Please place purchase orders for taping products per minimum order unit (1 reel or a case).

■ Packing Specifications


Taping

Number of packages (pcs.)			Tape width (mm)	Export package measurements (mm)
1 reel	1 case / Japan	1 case / export packing		
2,000	20,000	20,000	12	395 x 395 x 205




Drawing No. 1


■ Dimensions



■ Land Dimensions



■ Circuit Diagram



Viewed from switch mounting face