







Copyright FCI.



PC CARD DRILLING DIMENSIONS

Components side view - Thickness 1.60mm



LF FOR LEAD FREE

REQUIREMENTS

Technical characteristics:

- Material contacts: - brass
- Finish on contact area: -gold 0.76µ mini over nickel
- Finish on terminalson end: - bright tin - lead over nickel

Shell:steel tin/Zinc Cr3 plated

Insulators:self-extinguishing thermoplastic,ULClass94V0

Grounding brackets:brass,tin/Zinc Cr3 plated

Female screwlock:brass,tin/Zinc Cr3 plated

Harpoon: brass , tin plated

Climatic characteristics:

Operating temperature range:-55°C +125°C

Dimensions:

in accordance with MIL-C-24308

Part Number & Date Code Printing

Part number

DSWSP36A5GV08**

FOR ROHS DETAILS REFER DWG.N0:C01-8646-0000

European Views

rev	ecn no	dr	date
B	I05-0124	JS	2005/07/27
C	I06-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOHN SLEEBA	2001/02/06	ANGULAR		LINEAR	0.X	±0.1	size A3	Scale 1:1	
Eng	GEORGE VJ	2001/02/06				0.XX	±0.1			
Chr	GEORGE VJ	2005/07/27				0.XX' ±1°	0.XXX			
Appr	KVSD	2005/07/27	Product family					D-SUB	Spec ref -	
			title MALE CONNECT. 5W5 metal plate, harpoons,screwlock			dwg no C01-8646-0760			Rev. C	
			catalog no DELTA-D			CUSTOMER			sheet 1 of 1	

REV F - 2006-04-17