


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS		DATE	APPROVED



NOTES:
1. MATERIAL:

BNC MALE:
BODY :BRASS, NICKEL PLATED
CENTER PIN :BRASS, GOLD PLATED
CABLE:RG174/U
COLOR IS BLACK

THE TOLERANCE IS:
<1000 ±5
≥1000 ±10



No.	ACD No.	L(mm)	TITLE
12	CO-174BNCX200-025	7625	CA BNC M/BNC M RG174/U 25'
11	CO-174BNCX200-015	4575	CA BNC M/BNC M RG174/U 15'
10	CO-174BNCX200-012	3660	CA BNC M/BNC M RG174/U 12'
9	CO-174BNCX200-010	3050	CA BNC M/BNC M RG174/U 10'
8	CO-174BNCX200-007.5	2286	CA BNC M/BNC M RG174/U 7.5'
7	CO-174BNCX200-005	1525	CA BNC M/BNC M RG174/U 5'
6	CO-174BNCX200-004	1220	CA BNC M/BNC M RG174/U 4'
5	CO-174BNCX200-003	915	CA BNC M/BNC M RG174/U 3'
4	CO-174BNCX200-002.5	762	CA BNC M/BNC M RG174/U 2.5'
3	CO-174BNCX200-002	610	CA BNC M/BNC M RG174/U 2'
2	CO-174BNCX200-001.5	457	CA BNC M/BNC M RG174/U 1.5'
1	CO-174BNCX200-001	305	CA BNC M/BNC M RG174/U 1'

UNLESS OTHERWISE SPECIFIED EAR N.D.
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES	APPROVALS	DATE	Amphenol Cables on Demand 20 VALLEY ST. ENDOICOTT, NY 13760
.X ±.X	± °	DRAWN/INCH U	2006-11-18	
.XX ±.XX		CHECKED		
.XXX ±.XXX		RESP ENG		

TWO IN-LINE BNC (MOST
POPULAR)



THIRD ANGLE PROJECTION	WT G ENG	SIZE DWG. N.D.	REV.
		A	CO-174BNCX200-XXX

NOTES: UNLESS OTHERWISE SPECIFIED

CAD FILE:	SCALE	SHEET	OF