




CATALOG LISTING
424HE24-RB
PAGE 1 OF 1

ISSUE
5

REVISIONS

RASTER
DRAWN



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 5
 - 3 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 4 - CONNECTOR ELECTRONICALLY BONDED TO HOUSING
 - 5 - IN ADDITION TO STANDARD MARKING, CUSTOMER PART NUMBER AND CURRENT CUSTOMER DRAWING REVISION LEVEL IS MARKED ON THE SWITCH NAME PLATE IF APPLICABLE
 - 6 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
7 - $.010$ INCH OF PLUNGER TRAVEL
GOLD PLATED SILVER CONTACT BASIC SWITCHES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION	
CHARACTERISTICS			SCALE NONE	
OPERATING FORCE ——— 6 -12 LB			DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE--- 30 LB MAX			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ——— 4 LB MIN			ONE PLACE (.) $\pm .030$	
PRETRAVEL ——— .040 MAX			TWO PLACE (.) $\pm .015$	
DIFFERENTIAL TRAVEL ——— .020 MAX			THREE PLACE (.) $\pm .005$	
OVERTRAVEL ——— .250 MIN			ANGLES $\pm$	
ELECTRICAL DATA			WEIGHT .46 LBS MAX	
CONTACT ARRANGEMENT 4X S P D T 7			ANSI Y14.5M-1982 APPLIES	
28 VDC				
LOAD	SEA LEVEL	100,000 FT		
RES	7	7		
IND	4	4		
MOTOR	4	4		