

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	DR4/6.1.N.EX
Product ID:	1SNA146277R0700
EAN:	3472591462777
Catalog Description:	DR 4/6.1.N.EX Screw Clamp Terminal Blocks
Long Description:	DR4/6.1.N.Ex Screw Clamp Terminal Blocks Miniblocks.

Ordering

Color:	blue
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160004C0204
Instructions and Manuals:	1SNC160004C0204

Dimensions

Product Net Width:	6 mm
Product Net Height:	28 mm
Product Net Depth / Length:	26 mm
Product Net Weight:	6 g

Technical

Rated Cross-Section:	4 mm ²
Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Miniblock
Number of Levels:	1
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225054U1001
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220001E1002
Instructions and Manuals:	1SNC160004C0204
RoHS Information:	1SND230023F0201

Classifications

Object Classification Code:	X
-----------------------------	---

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	66 mm
Package Level 1 Depth / Length:	150 mm
Package Level 1 Height:	41 mm
Package Level 1 Gross Weight:	0.3 kg
Package Level 1 EAN:	3472591462777
Package Level 2 Units:	1750 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 2 Gross Weight:	10.5 kg
Package Level 3 Units:	84000 piece
Product Packing Type:	Box

