



Part Number : [190370004](#)
Product Description : Krimptite Snap Receptacle,
for 16-14 AWG Wire, Box, 16.26mm Length, Carton
Series Number : 19037
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : BB-1122



Documents and Resources

Drawings

[190370004 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19037
Description	Krimptite Snap Receptacle, for 16-14 AWG Wire, Box, 16.26mm Length, Carton
Product Name	Krimptite
Type	Snap Receptacle
UPC	800755059014

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	N/A
-------------------	-----

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None

Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.617/g
Orientation	Straight
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Wire Insulation Diameter	N/A
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640031100</u>
Hand Crimp Tool	<u>640031200</u>

This document was generated on Apr 23, 2026