

**ML-800-S1H****ML-800-S3H****ML-800-S1V****ML-800-S3V**

Enlarge : Click picture, drawing.

| [Back](#) | [List](#) | [Next](#) |

To be Followed by part number.





Body color



Item	ML-800	
Specification	S1H/S1V	S3H/S3V
Rating	250V-10A	
With standing V	AC2000V(1minute)	
Insulation Ω	DC500V,100M Ω Min	
Contact Ω	20m Ω Min	
Safety approvals	UL(Factory & Field),CSA,TÜV(IEC947-7-1)	
Number of poles	1 up to 30	2 up to 15
Insulation materials	Body:Nylon66(UL94V-0),Knob:PPHOX(UL94V-0)	
Reccommended wire Gage	Solid wire ϕ 1.2mm(AWG16),Stranded wire:1.25mm ² (AWG16)Element wire ϕ 0.18Min	
Acceptable wire Gage	Solid wire: ϕ 0.4mm(AWG26) up to ϕ 1.2mm(AWG16) Stranded wire:0.2mm ² (AWG24) up to 1.25mm ² (AWG16)Element wire ϕ 0.18Min	
Stripping length	11mm	
Pitch	5mm	10mm
Terminal style	PCB	
Body color	Standard color: Beige (LB) Custom color: Black(B),White(W),Red(R),Yellow(Y),Green(G),Blue(BL),Pink(PK),Lime (LG),Purple(VI),Orange(OR),Brown(BR)	
End plate Color	Beige (LB)	
Knob Color	Gray	
Check hole	無し	
Recommended tools	Screw driver ϕ 3	
Optional accessories	ML-1000-L1(Polarizing Key)	
	チェックピン仕様(特注品)	
	基板取付モールド(特注品)	
Feature	本体の形式として電線の接続方法がトップエントリーとなるV(縦型)タイプ、サイドエントリーとなるH(横型)タイプの2タイプあり、実装用途に合わせた選択が出来ます。 本体の標準色はBeigeで、標準色以外(カラーコンビネーションを含む)は特注となります。	
Important notice	Do not wash	

How To Order

ML - 800 - 			
Series	接続形式と端子間ピッチ	Style	Number of poles
ML - 800	S1:1線接続で5mmピッチ	H : Horizontal	1 up to 30
	S3:1線接続で10mmピッチ	V : Vertical	2 up to 15

ML-800-S1H**ML-800-S3H****ML-800-S1V****ML-800-S3V**

UP DATE: 6/30/2006

[Back](#)[Home](#)

- The contents of these document are subject to change without previous notice for improvements in product performance.
- When using the products, please confirm with the specifications which will be provided to you upon request. Individual specifications prior to the catalog specification.
- The appearance of product's color may differ from original upon your monitor or operating system.
- The latest information to receive please consult our marketing either phone call or e-mail.

e-mail: marketing@satoparts.co.jp

[| Company profile](#) | [| Site map](#) | [| Ask](#) | [| Notice and hint](#) | [| Renewal record](#) | [| Japn Web site](#) |

Copyright(C)2001-2006 SATO PARTS CO.,LTD.All Right Reserved.