

Technical data sheet

Article number:
151-02606

CDC22S40.5M10

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Bundle Ø max.	22.0 mm
Fixation Method	screwable
Flammability	UL 94 V2
for Hole Ø (FH)	10.6 mm
Height (H)	72.8 mm
Length (L)	72.7 mm
Mounting Screw Type	M10 Screw
Operating Temperature	-40 °C to +105 °C
Package Content	500 pcs.
Package Content packed in	carton
ROHS compliant	Yes
Width (W)	23.0 mm

RoHS 