





TABLE 1				
KEYING LETTER	A°	B°	C°	COLOR BAND
NONE	120°	120°	120°	NONE
S	135°	135°	90°	WHITE
T	100°	150°	110°	RED
U	120°	130°	110°	ORANGE
V	115°	130°	115°	YELLOW
W	125°	110°	125°	GREEN
X	130°	100°	130°	BLUE
Y	110°	140°	110°	VIOLET
Z	100°	160°	100°	GRAY

TABLE 2	
INCH	MM
.005	0.13
.015	0.38
.030	0.76
.036	0.91
.062	1.57
.125	3.18
.140	3.56
.187	4.75
.190	4.83
.380	9.65
.439	11.15
.443	11.25
.487	12.37
.500	12.70
.562	14.27
.600	15.24
.892	22.66
1.00	25.40
1.122	28.50

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS				3-0001	SH 1
REV	ECO NO.	DESCRIPTION	DWN	APROVED	DATE
X	54057			P. KLYVE	12/18/13



RECOMMENDED
PANEL CUTOUT
SCALE 2.000

- 4. MAX PANEL THK .125
- 3. SOCKET CONTACT CONCENTRIC TWINAX/ TRIAX TRB SOLDER POT BULKHEAD MOUNT RECEPTACLE
- 2. FINISH: TFS-1A(NICKEL)
- 1. ALL DIM ARE IN INCHES

5. EXAMPLE OF COMPLETE MODEL NO:

BASIC MODEL NO. **BJ77 - T** POLARIZATION LTR (SEE TABLE 1)

QTY		DESCRIPTION			PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ± .005 .XXXX ± ANGLE ±			TROMPETER ELECTRONICS, INC.®		BJ77/S/T/U/V/ W/X/Y/Z		
DWG	CWW	12/19/13	MATERIAL —	CODE IDENT 14949	DRAWING NO. 3-0001		REV X
CHK	PAK	12/19/13					
SEE SH 3	ENGR						
NEXT ASSY	APPR			SCALE 4/1	DATE 11-12-68	SHEET 1C	