

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Socket
- Plug
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >
- ALTW Emporium >



ZA-AANMAN-BN0001

- Operating Temperature: -40°C ~ +110°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

ZConnect. Socket..
ZA-20BFRS-...
-40°C ~ +110°C

- 0 +

Add to Cart

ZConnect. Socket..
ZA-40AFRS-...
-40°C ~ +110°C

- 0 +

Inquiry

Specifications	Download / CAD
Nominal Current 1A	Connector Type Plug
Shielded Plastic, Non-shielded	No. of Contacts N/A
Connector Gender Male	Backshell N/A
Mating Style Quick Lock	IP Rating N/A
Assembly Style N/A	
+ More Options	

People Also Bought

- ZA-AANMAN-BN0001
- AB-BB03FL-BBHL-...
- ABD-03AFFM-LL7A10
- 1CD-09BMMM-...
- ABB-03AFMM-...