




99M0111-24-45 Product Details

[Share](#) [Print](#) [Email](#)


99M0111-24-45

TE Internal Number: 2813293001

 Active

Spec 99 and Spec 100 Wire and Cable

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Cable Type = Spec 99M
- Cable Style = Primary
- Wire Size (AWG or Metric) = 24 AWG [0.24 mm²]
- Number of Conductors = 1
- Equipment Wire Application

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Customer Drawing](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Cable Type = Spec 99M
- Cable Style = Primary

Electrical Characteristics:

- Wire Size (AWG or Metric) = 24 AWG [0.24 mm²]
- Voltage Rating (VAC) = 600

Dimensions:

- Conductor Outer Diameter (mm [in]) = 0.64 [0.025]

Body Features:

- Wire Color = Yellow w/ Green Stripe
- Nominal Outside Diameter (mm [in]) = 0.89 [0.035]
- Wire Diameter (mm [in]) = 0.89 [0.035]
- Conductor Type = Tin-Plated Copper

Configuration Features:

- Number of Conductors = 1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Wire Size - Details = 24 AWG 0.24 mm², 0.00037 in², 19 x 36 AWG
- Temperature Range (°C) = -55 - +125

Operation/Application:

- Application = Equipment Wire

Packaging Features:

- Wire Source = United Kingdom

Other:

- Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

