

- Feature
- Browse by Category
- Browse by Application
- Shore

Search →

Enter part number or keyword

- Search Results (0)
- Search Options

No Search Results

Select a product type to narrow your search:

Connector

Results with your selections: --

Family

- ☐ 0.64
- ☐ 040
- ☐ 070
- ☐ 56
- ☐ 59
- ☐ 090
- ☐ 187
- ☐ ACT
- ☐ APEX
- ☐ ATS
- ☐ Apex
- ☐ BTS
- ☐ Bus-Bar
- ☐ CTS
- ☐ Coax
- ☐ DCK
- ☐ DCS-1
- ☐ DCS-2
- ☐ DS
- ☐ DSQ
- ☐ Ducon
- ☐ DuoTwin
- ☐ Fakro
- ☐ Flexible Power
- ☐ Fuse
- ☐ GT
- ☐ GT Flex Beam
- ☐ GTS
- ☐ GTS-2
- ☐ GTS-3
- ☐ HES
- ☐ HPCS
- ☐ HVISO
- ☐ High Power
- ☐ High Voltage
- ☐ Hyllok
- ☐ IDC
- ☐ Lamp Socket
- ☐ MCS
- ☐ MTS
- ☐ MTS-B
- ☐ Metri-Pack
- ☐ Micro
- ☐ Micro HVT
- ☐ Micro-Pack
- ☐ Mixed
- ☐ Modupack
- ☐ OCS
- ☐ Pack-Con III
- ☐ Performance Pack
- ☐ Power Pack
- ☐ RCS800
- ☐ RCS890
- ☐ Shield-Pack
- ☐ Sigma
- ☐ Sleeve
- ☐ Sleeve / Pin
- ☐ Squib / Interface-ABX UC
- ☐ Squib / Interface-ABX-3
- ☐ Squib / Interface-AK-1
- ☐ Squib / Interface-AK-2
- ☐ Squib / Interface-AK-2+
- ☐ Squib / Interface-FCI
- ☐ TTS
- ☐ Timer
- ☐ UC
- ☐ USB 2.0
- ☐ USCAR
- ☐ VF
- ☐ Weather Pack
- ☐ ZRT



Search → Clear

Cavities

- ☐ 1
- ☐ 2
- ☐ 2
- ☐ 3
- ☐ 4
- ☐ 5
- ☐ 6
- ☐ 7
- ☐ 7
- ☐ 8
- ☐ 9
- ☐ 10
- ☐ 11
- ☐ 12
- ☐ 13
- ☐ 14
- ☐ 15
- ☐ 16
- ☐ 17
- ☐ 18
- ☐ 19
- ☐ 20
- ☐ 21
- ☐ 22
- ☐ 23
- ☐ 24
- ☐ 25
- ☐ 26
- ☐ 27
- ☐ 28
- ☐ 29
- ☐ 30
- ☐ 31
- ☐ 32
- ☐ 34
- ☐ 35
- ☐ 36
- ☐ 37
- ☐ 38
- ☐ 39
- ☐ 40
- ☐ 41
- ☐ 42
- ☐ 44
- ☐ 45
- ☐ 46
- ☐ 47
- ☐ 48
- ☐ 49
- ☐ 50
- ☐ 52
- ☐ 54
- ☐ 55
- ☐ 56
- ☐ 57
- ☐ 58
- ☐ 59
- ☐ 60
- ☐ 62
- ☐ 63
- ☐ 64
- ☐ 65
- ☐ 66
- ☐ 68
- ☐ 72
- ☐ 73
- ☐ 74
- ☐ 76
- ☐ 78
- ☐ 80
- ☐ 81
- ☐ 92
- ☐ 84
- ☐ 90
- ☐ 96
- ☐ 100
- ☐ 108
- ☐ 112
- ☐ 116
- ☐ 120
- ☐ 130
- ☐ 133
- ☐ 154
- ☐ 162
- ☐ 169
- ☐ 202



Search → Clear

Gender

- ☐ Female
- ☐ Female + Female
- ☐ Male
- ☐ Male + Female
- ☐ Male + Male



Search → Clear

Sealed

- ☐ Sealed
- ☐ Unsealed



Search → Clear

Terminal(s) blade size [mm]

☐ Mixed - Results will have exactly your selections in the same connector.

- ☐ 0.50
- ☐ 0.64
- ☐ 0.8
- ☐ 1.0
- ☐ 1.0 (round)
- ☐ 1.2
- ☐ 1.5
- ☐ 1.8
- ☐ 2.0 (round)
- ☐ 2.3
- ☐ 2.5
- ☐ 2.6
- ☐ 2.8
- ☐ 4.1
- ☐ 4.8
- ☐ 5.7
- ☐ 6.3
- ☐ 8.0
- ☐ 9.5
- ☐ 10.0
- ☐ 20.0



Search → Clear

Product Segment

- ☐ Headers
- ☐ High Power
- ☐ Safety Restraint Systems (SRS)
- ☐ Standard Automotive



Search → Clear

Application

- ☐ A/C Compressor
- ☐ Actuator
- ☐ Aerial / Antenna
- ☐ Airbag
- ☐ Alternator
- ☐ Antenna - Keyless System
- ☐ CAN
- ☐ Camera
- ☐ Cigar Lighter / Power Outlet
- ☐ Diagnostic
- ☐ Door To Body
- ☐ Electrovalve - Cold Start
- ☐ Fan - Engine Cooling
- ☐ Harness - Roof
- ☐ Heater - Rear Window
- ☐ Horn
- ☐ Ignition Coil
- ☐ Immobilizer
- ☐ Injector
- ☐ Inliner
- ☐ Instrument Cluster
- ☐ Lamp - Interior Lamp
- ☐ Lamp - Socket
- ☐ Latch
- ☐ Mirror
- ☐ Module - ABS
- ☐ Module - Airbag
- ☐ Module - Engine
- ☐ Module - Exterior
- ☐ Module - Interior
- ☐ Module - Transmission
- ☐ Motor - Blower
- ☐ Motor - Seat
- ☐ Motor - Wiper
- ☐ Multimedia
- ☐ Pad - Heated Seat
- ☐ Pump
- ☐ Relay
- ☐ Sensor - Accessories
- ☐ Sensor - Brakes
- ☐ Sensor - Crash
- ☐ Sensor - Engine
- ☐ Sensor - Exhaust
- ☐ Sensor - Exterior
- ☐ Sensor - Interior
- ☐ Sensor - Transmission
- ☐ Socket - Multimedia
- ☐ Socket - Tow Bar
- ☐ Speaker
- ☐ Starter
- ☐ Switch
- ☐ Switch - Multifunction



Search → Clear

Clear Search →

48 Way CMC sealed Connector, black keyway, left lever



Part #PPI0001494

Question about this product?

- Attributes
- Documents (1)
- Related Products (11)

Part #:	PPI0001494
Description:	48 Way CMC sealed Connector, black keyway, left lever
Product Type:	Connector
Status:	Active
Family:	GTS
Series:	Mixed
Cavities:	48
Terminal(s) blade size [mm]:	0.64, 1.5
Sealed:	Sealed
Gender:	Female
Temperature range [°C]:	-40 to +125
Material:	PBT
Color:	Black
Application:	Module - ECM (PCM)
Remarks:	Former FCI Product, Delphi PN:13956021, Sealed Connector for Electronic Control Unit Applications, Silicon Rubber Seal, 24X0, 64mm Signal Circuits, 8X1, 5mm Power Circuits, Accepts Reversible Dress Cover, Right or Left Mounted Mate - Assist Lever Versions Available, Suitable for Harsch Environment, - 40/+125°C Temperature Resistant, 15G Sinus Vibration Resistant with Tin Terminals, 1, 5 Bar Pressure Sealing.

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.