



UNLESS OTHERWISE SPECIFIED:
 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
 3 PLACE DECIMALS $\pm .004$
 1. 1. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES
 2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX
 3. NO FILLETS PERMITTED.
 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
 5. ALL DIMENSIONS PRIOR TO PLATING.
 6. ALL PLATING IN ACCORDANCE WITH KER 10004.

KC-79-179 (SMT 1 OF 2)

S-D

REVISIONS	
DATE	DESCRIPTION
2	CN/9855C M.A. 19 JAN 80 REDRAWN
3	CN 21964C GJG 18 MAY 81
4	CN 22827C MD 7 DEC 81

SCALE 4:1

UNLESS OTHERWISE SPECIFIED

REV

BNC BULKHEAD
 RECEPTACLE

DRAWN BY: JTB SMT 6 DEC 79
 APPR: JMD DATE 13 DEC 79

WINCHESTER ELECTRONICS CORP. INC.
 1511-1515 CHAS. ST. NEW YORK, NY 10013

KC-79-179

(SMT 1 OF 2)

