








HOLE LAYOUT



CIRCUIT DIAGRAM

C: COMMON PIN
BOTTOM VIEW



Specifications:

Contact rating:	0.2A, 30V DC
Contact resistance:	30mOhm max.
Insulation resistance:	100MOhm min. at 500V DC for 1 minute
Dielectric strength:	500V AC (50/60Hz, 2mA) for 1 minute
Operating temperature:	-10°C to +70°C
Mechanical life:	10 000 cycles
Operating force:	200 +/-100gf
Soldering conditions:	260 +/-5°C, 5 +/-1sec.
Material:	Spring plate: stainless steel, washing Terminal: brass strip, silver plated Base: phenolic resin, natural Contact clip: phosphor bronze, silver plated Frame: steel, tin plated Slider: PBT, black

Compliance: RohS III (2015/863/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm	Date	Name
	02/13	dr
Operating temperature	06/19	dr
Modifications	Date	Name

MFP 421 N-RA

knitter-switch

30 27 91

Page

1/1