

Fixed Wall-Mount Rack Cabinet (130 lb) *RB-FW Series*

Simple, fixed-position wall-mount rack for secure and reliable installation of network and telecom equipment.

Key Features and Benefits



- 16-gauge steel construction (130 lb capacity) provides reliable support for switches, patch panels, and rack-mounted equipment.
- 19" rack compatibility with square-hole (M5) mounting rails supports standard equipment and flexible positioning.
- Fixed wall-mount cabinet design maintains consistent equipment alignment for structured installations.
- Locking tempered glass front door and removable side panels provide physical security and controlled access.
- Integrated ventilation with optional fan provisions supports airflow and thermal management.
- Rear cable access enables organized cable entry and routing.
- Includes hardware pack for installation and equipment mounting.
- RoHS compliant supports environmental compliance requirements.

The RB-FW Series fixed wall-mount rack is a simple, reliable solution for mounting 19-inch rack equipment in network closets, telecom rooms, and commercial IT environments. Its fixed-position design supports consistent equipment alignment while maintaining open access for installation, servicing, and cable routing.

RACK BASICS®

A HAMMOND BRAND



Rack Mounting
Hardware Included




When Another Product May Be a Better Choice

- When you need swing-out access for easier rear equipment access, consider our **RB-SW** or **RB-SWDV** Series.
- When you need higher load capacity, seismic load ratings, or dust protection, consider our **HWC** Series wall-mount cabinets.
- When you need environmental protection against dust or water, consider our **NWC** or **NWM** Series cabinets.

Part of the Rack Basics® line designed for simple, reliable, and affordable installations.

Accessories

- Horizontal Cable Manager Ring Style
- Horizontal Cable Lacing Bar Steel Cable Support Bar
- Rack Cabinet Cooling Fan Kits
- We Manufacture PDUs and Outlet Strips
- Horizontal Cable Management Bar Steel Cable Support Bar
- Universal Rack Shelf Fixed Steel (Up to 200 lb Capacity)
- Hardware for Rack Mounting Solutions



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
RB-FW6	14.65	23.62	23.62	6U	10.50	19.00	21.24
RB-FW9	19.90	23.62	23.62	9U	15.75	19.00	21.24
RB-FW12	25.15	23.62	23.62	12U	21.00	19.00	21.24
RB-FW15	30.40	23.62	23.62	15U	26.25	19.00	21.24

Mounting Dimensions / Usable Depth is the maximum allowable equipment depth.

Where the RB-FW Series Works Best

- Network closets and IT rooms.
- Telecom backboards and communication areas.
- Office and commercial IT environments.
- Structured cabling installations.
- Applications requiring fixed equipment positioning.

Applications and when to use the RB-FW Series

- You need a fixed-position wall-mount rack for consistent equipment alignment.
- Equipment installations require stable, non-adjustable mounting.
- You need front-access installation and cable management in a fixed wall-mount cabinet design.
- Space is limited but a more secure mounting solution than basic brackets is required.

Tags: **Wall-mount cabinet, fixed wall-mount rack, 19" wall rack, network cabinet, telecom wall cabinet, enclosed wall rack, server wall cabinet, lockable wall cabinet, structured cabling cabinet, IT wall enclosure**

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.