



Common Mode Choke

TCK-138



Order Code	TCK-138
Inductance (each winding)	18.2 μ H $\pm$ 25% (at 100 kHz / 1 V)
Impedance (DCR)	10.5 m Ω max.
Rated Current	1.44 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-138



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	6.5 $\pm$ 0.3
B	6.0 $\pm$ 0.2
C	4.5 max.
D	4.3
E	7.7
F	0.91
G	3.0

All specifications valid at +25°C, unless otherwise stated.