

Specifications

Eaton CL0904-2-50TR-R

Eaton CL0904 inductor, 50 nH, 0.35 mΩ resistance, Two-phase



General specifications

PRODUCT NAME	Eaton CL0904 inductor
CATALOG NUMBER	CL0904-2-50TR-R
UPC	051712295574
PRODUCT LENGTH/DEPTH	20 mm
PRODUCT HEIGHT	4 mm
PRODUCT WIDTH	9 mm
PRODUCT WEIGHT	2.71 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Two-phase
ISAT	5 A
PACKAGE QUANTITY	1000
MATERIAL	Ferrite
CONTACT CONFIGURATION	Four-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.35 mΩ
TERMINALS	Four
INDUCTANCE	50 nH
SERIES	CL0904

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
CL0904-2-50TR-R](#)

[Eaton CL0904 mutli-phase
power inductor data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

