



**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL


FED. MFG. CODE 91829

SWITCH - BASICCATALOG LISTING
3TB41-156-32 UNC X
.250 REF BINDING HEAD
TERMINAL SCREW (2)

PLASTIC PLUNGER

**NOTE**

1 - TERMINALS 3 & 4 NORMALLY OPEN

**CIRCUIT DIAGRAM**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 7-13 OZ

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL - - - - .010-.025

OVERTRAVEL - - - - - .010 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
SEE CIRCUIT DIAGRAML25 10A-125 OR 250 VAC
1/2HP-125 VAC**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .02 LB

3TB41-15**M**DRAWING
NUMBERISSUE
*2

REVISIONS

A 0059824
JAS
18 SEPT 86

REPLACES X77522-TB

RELEASE NO. PR-12691

CHECK

CHECK

JAN 84

JAN 84

JAN 84

JAN 84

JAN 84

DRAWN

0378