



SAE-20 Series

SAE-20D

- Dynamic Speaker
- Non-washable
- Heat Resistant
- Reflow
- High SPL
- Automotive Use

* As for non washable products, dip soldering should not be implemented.



We may use unique personal identifiers (such as cookies) in order to analyze our website traffic and to personalize content and ads, and may share information about your use of our website with our analytics and advertising partners. These partners may combine this information with other data you have provided or gathered from your use of their services. You have the right to opt out of our sharing of your information with these partners by clicking on [Do Not Sell or Share My Personal Information].

Do Not Sell or Share My Personal Information

Close

1K, 1.6K, 2K, 3.2Khz)

Dimensions (size: 20×20×4.7mm)

(SAE-20D)

(SAE-20D)

20

20

24 × φ 1.2

Sound port

4.7

4 × 1.5

Dummy Lead

4 × 3

14

Lead

Lead

unit: mm/housing material: LCP

Input : 0.5W
Back cavity : Free
Mic. Distance : 10mm

SPL (dB)

Frequency (Hz)

125

120

115

110

105

100

95

90

85

80

100

1000

10000

115

110

105

100

95

90

85

80

SAE-20D

- Dynamic Speaker
- Non-washable
- Heat Resistant
- Reflow
- High SPL
- Automotive Use


* As for non washable products, dip soldering should not be implemented.



Specifications

* Value applying nominal input (sine wave, average of 1K, 1.6K, 2K, 3.2Khz)

Frequency Response



Dimensions (size: 20×20×4.5mm)



Inquiry

We will propose the optimal product tailored to your needs. Please feel free to contact us.

Product Inquiry



Micro Speakers >

SAE-20 Series >

SAQ-37 Series >

SAN-15 Series >

SAL-40 Series >

SAC-30 Series >