



HONEYWELL PART NUMBER
311SM717-T
PRODUCT CODE TZA2708

REV	DOCUMENT	CHANGED BY	CHECK
7	0038115	VS 28APR08	BLR



NOTE -
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
2- TERMINALS ARE PLATED FOR SOLDERING
3- MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY
4- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.
PR - 6589

REPLACES

CHARACTERISTICS
OPERATING FORCE - - 6 GRAM MAX
RELEASE FORCE - - - - 1 GRAM MIN
DIFFERENTIAL TRAVEL - - - .070 MAX
OVERTRAVEL - - - - - .057 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT SPDT		
30 VOLTS DC RATING		
	SEA LEVEL	50,000 FT
INDUCTIVE	1/2 AMP	1/2 AMP
RESISTIVE	1 AMP	1 AMP
MAXIMUM INRUSH 2 AMP		
APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4
	UL, CSA	1A, 125 VAC

DESIGN UNITS: INCH		
TOLERANCES UNLESS NOTED:		
NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±
THIRD ANGLE PROJECTION		

DRAWN	VK	21 NOV 07
CHECK	RJ	21 NOV 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE B	TYPE I	DRAWING NAME 311SM717-T	REV 7
SCALE -	WEIGHT .006 LB MAX	SHEET 1 OF 1	