



search



live chat offline

HOME

CURRENT

COMPANIES

DOWNLOAD


PRODUCTS

DISTRIBUTORS / DISTRIBUTORS

DISTRIBUTION

CONTACT

BACK



B6B-PH-SM4-GW-TBT (LF) (SN)

Description: With suction tape, 0.2AU

Header PH 2.0 SMT top entry

specification

Grid (mm)	2.0
Connector Type	WTB
Number of poles	6
Current (A)	2
Voltage (V)	100
Connection Type. (THT / SMT)	SMT
Cross-section (AWG)	32-24
Lying version	0
Straight version	-1
Water proof	0
Single row	-1
Double row	0
ZIF	0
Non-ZIF	0

UP

Products

FOR PC BOARD
WIRE TO WIRE
WATERPROOF CONNECTORS
LOOSE PIECE TERMINALS
CHAIN TERMINALS
CARD AND INTERFACE CONNECTORS
HIGH VOLTAGE SHIELDED SEALED CONNECTOR
AUTOMOTIVE

information

DOWNLOAD
IMPRINT
DATA PROTECTION

Newsletters

V orname

Nachname

E-Mail Adresse

Sign in

