

5.08 MIN
[.200] TYP

3.81 MIN
[.150] TYP

LOCALIZED
PLATE AREA

GOLD FLASH
TYP

1.27
[.050]
MAX TYP

GOLD FLASH
TYP

DETAIL V
SCALE 10:1

-

OBSOLETE	53.34	71.12	65.02	75.18	71.12	60.96	44	1-499206-3
	[2.100]	[2.800]	[2.560]	[2.960]	[2.800]	[2.400]		
	78.74	96.52	90.42	100.58	96.52	86.36	64	1-499206-2
	[3.100]	[3.800]	[3.560]	[3.960]	[3.800]	[3.400]		
	73.66	91.44	85.34	95.50	91.44	81.28	60	1-499206-
	[2.900]	[3.600]	[3.360]	[3.760]	[3.600]	[3.200]		
	60.96	78.74	72.64	82.80	78.74	68.58	50	1-499206-0
	[2.400]	[3.100]	[2.860]	[3.260]	[3.100]	[2.700]		
	48.26	66.04	59.94	70.10	66.04	55.88	40	499206-9
	[1.900]	[2.600]	[2.360]	[2.760]	[2.600]	[2.200]		
	40.64	58.42	52.32	62.48	58.42	48.26	34	499206-8
	[1.600]	[2.300]	[2.060]	[2.460]	[2.300]	[1.900]		
	35.56	53.34	47.24	57.40	53.34	43.18	30	499206-7
	[1.400]	[2.100]	[1.860]	[2.260]	[2.100]	[1.700]		
	30.48	48.26	42.16	52.32	48.26	38.10	26	499206-6
	[1.200]	[1.900]	[1.660]	[2.060]	[1.900]	[1.500]		
	27.94	45.72	39.62	49.78	45.72	35.56	24	499206-5
	[1.100]	[1.800]	[1.560]	[1.960]	[1.800]	[1.400]		
	22.86	40.64	34.54	44.70	40.64	30.48	20	499206-4
	[.900]	[1.600]	[1.360]	[1.760]	[1.600]	[1.200]		
17.78	35.56	29.46	39.62	35.56	25.40	16	499206-3	
[.700]	[1.400]	[1.160]	[1.560]	[1.400]	[1.000]			
15.24	33.02	26.92	37.08	33.02	22.86	14	499206-2	
[.600]	[1.300]	[1.060]	[1.460]	[1.300]	[.900]			
10.16	27.94	21.84	32.00	27.94	17.78	10	499206-1	
[.400]	[1.100]	[.860]	[1.260]	[1.100]	[.700]			
	F	E	D	C	B	A	NO OF POSN	PART NUMBER

Downloaded from Arrow.com.