






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL VERSION RELEASE	28SEP2023	F.Y	C.W




- NOTE:
- MATERIAL:
CONTACT BODY: COPPER ALLOY
LOCKING SPRING: STAINLESS STEEL
 - SURFACE PLATING:
a) NICKEL UNDERPLATING, GOLD PLATING AT CONTACT AREA, TIN PLATING AT OTHER AREA.
b) NICKEL UNDERPLATING, TIN PLATING OVERALL.
 - PACKAGE: 4000PCS/REEL, 8000PCS/BOX

- 注释
- 材料
端子主体：铜合金
锁扣弹片：不锈钢
 - 电镀规格：
a) 底镀镍，接触区镀金，其他区域镀锡
b) 底镀镍，全镀锡
 - 包装：4000pcs/卷, 8000pcs/箱



SECTION C-C
SCALE 10:1



SECTION D-D
SCALE 10:1

Ø 2.7	4.27	4.20	Ø 1.10	2.41	2.28	(b)	Ø 1.0MM FEMALE STAMPING CONTACT TIN PLATED, 0.50~0.75MM ² ,	T2210002010-041
						(a)	Ø 1.0MM FEMALE STAMPING CONTACT GOLD PLATED, 0.50~0.75MM ²	T2210002010-040
Ø 2.6	4.27	4.20	Ø 0.80	1.75	1.85	(b)	Ø 1.0MM FEMALE STAMPING CONTACT TIN PLATED, 0.20~0.35MM ²	T2210002010-031
						(a)	Ø 1.0MM FEMALE STAMPING CONTACT GOLD PLATED, 0.20~0.35MM ²	T2210002010-030
DIM.F	DIM.E	DIM.D	DIM.C	DIM.B	DIM.A	SURFACE PLATING	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN FENCER YU 28SEP2023	TE Connectivity				
DIMENSIONS: mm			CHK CHRIS WANG 28SEP2023					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD CHRIS WANG 28SEP2023	NAME 1MM FEMALE STAMPING CONTACT				
0 PLC ±0.50 1 PLC ±0.30 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±			PRODUCT SPEC 108-137685	SIZE A2				
MATERIAL SEE NOTE material_2			APPLICATION SPEC 114-137685	CAGE CODE 00779				
FINISH -			WEIGHT -	DRAWING NO C-T22100020100XX				
finish_spec_2			CUSTOMER DRAWING	SCALE 6:1		SHEET 1 OF 1		REV A