


HONEYWELL
PART NUMBER
BZ-7RW825520-A2-S


REV	DOCUMENT	CHANGED BY	CHECK
A	0041984	SS 24JUL08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

CATALOG LISTING AQL9302
REPLACES X201403-BZ

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	SS	24JUL08	Honeywell							
		CONTACT ARRANGEMENT S P D T				CHECK	BD	24JUL08								
OPERATING FORCE----- 5 OZ MAX		L96 15A 125, <u>250</u> OR 480 VAC 1/8 HP <u>125</u> VAC, 1/4 HP <u>250</u> VAC 1/2A 125 VDC, 1/4A 250 VDC L288 L315 L306  16A 250V  T85 5E4		NO PLACES X ± -		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH, BASIC						
RELEASE FORCE----- 3/4 OZ MIN				ONE PLACE .X ± .03												
DIFFERENTIAL TRAVEL----- .040 - .062				TWO PLACE .XX ± .015		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	CAGE CODE	DRAWING NAME			REV
OVERTRAVEL----- .156 MIN				THREE PLACE .XXX ± .005						B	I	-	BZ-7RW825520-A2-S			A
		THIRD ANGLE PROJECTION 		RASTER				SCALE	-	WEIGHT	.076 LB	SHEET	1	OF	1	