



REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-013292	16SEP2015	DL	CW
	BI	ECR-16-009730	06JUL2016	BS	CW
	C	ECR-21-105750	02JUL2021	BS	CW
	D	ECR-25-246911	26JUN2025	ABS	RB

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PBT
RATED VOLTAGE: 50 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 0.8 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X20XX000)

- 注释:
1. 技术参数:
绝缘材料: PBT
额定电压: 50V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 0.8 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20200X20XX000)



M3 SCREW
RECOMMENDED TIGHTENING
TORQUE 0.5Nm



T2020082201-001	HD-008-F HD-008母插(不锈钢螺丝)
T2020082201-000	HD-008-F HD-008母插
PART NUMBER 料号	DESCRIPTION 描述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16DEC2014 RAGHAVENDRA H M	 TE Connectivity		
		CHK 16DEC2014 CHRIS WANG			
		APVD 16DEC2014 XU XIANG	NAME HD-008-F		
		PRODUCT SPEC 108-137042			
		APPLICATION SPEC 114-137042			
		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO T2020082201000
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV D

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	±0
		1 PLC	±0
		2 PLC	±0
		3 PLC	±0
		4 PLC	±0
		ANGLES	±0
		FINISH	-
			-