

RATING: 100 VAC 1A

INSULATION RESISTANCE:

50 Megaohm min. @250, VDC

CONTACT RESISTANCE:

30 million Max.




DIELECTRIC STRENGTH:

250 VAC for one minute.

INSERTION FORCE:

4.5 Kgf Max.

EXTRACTION FORCE:



TOLERANCE	SCALE	DATE	DESING	DRAW	INSPE	APRO
±0.3	2/1			N.1		

MODEL 型式	QTY	PART NAME 品名	MJ381/3~8
MATERIAL 材質	DRAW. NO 図番		MJ381
FINISH 処理	 MARUSHIN ELECTRIC MFG. CO., LTD.		

4	NUT	STEEL	1	Uni-Chrome
3	CONTACT	Phosphor Bronze	3~8	Ag
2	SHIELD	BRASS	1	Sn
1	HOUSING	P.B.T	1	
LET	PART NAME	MATERIAL	QTY	FINISH
				NOTE

EST. MARUSHIN ELECTRIC MFG. CO., LTD.