

SATO PARTS CO.,LTD. > Product Category > Screwless Terminal Blocks


Product mass

Precautions for use

General notes

ML-950

made in JAPAN



Pitch 5mm

Stranded wire and Solid wire

Check hole

Press fit

2013-01-25

Notice of partial product changes. PDF

See other change notifications

E101073

LR65928

Order model number

Order model numberML-950-[Position]

Order exampleML-950-2P (An example of ordering with 2 positions.)


- Basic information
- Dimension
- Soldering heat resistance conditions
- Download

Dimension

Add to My List

Sample request (Only available in Japan)

Unit:mm




Dimension table

Unit:mm

極数 [P]	A	B	極数 [P]	A	B	極数 [P]	A	B	極数 [P]	A	B
1	6.6	-	6	31.6	25.0	11	56.6	50.0	16	81.6	75.0
2	11.6	5.0	7	36.6	30.0	12	61.6	55.0	17	86.6	80.0
3	16.6	10.0	8	41.6	35.0	13	66.6	60.0	18	91.6	85.0
4	21.6	15.0	9	46.6	40.0	14	71.6	65.0	19	96.6	90.0
5	26.6	20.0	10	51.6	45.0	15	76.6	70.0	20	101.6	95.0

Related products


ML-1400-S1



ML-1400-S1

Add to My List


ML-1400-S1L



ML-1400-S1L

Add to My List

ML-2100



ML-2100

Add to My List