



REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	07/31/15	J. C.
B	Added Color Options, Sheet #2	01/25/16	J. C.
C	ECO-1401 Updated Color Options	07/24/26	A. V.



Part No.	X = Body Length
PLPQ2-100	0.100 (2.5mm)
PLPQ2-125	0.125 (3.2mm)
PLPQ2-188	0.188 (4.8mm)
PLPQ2-250	0.250 (6.4mm)
PLPQ2-313	0.313 (7.9mm)
PLPQ2-375	0.375 (9.5mm)
PLPQ2-500	0.500 (12.7mm)
PLPQ2-3MM	3mm (0.118\"
PLPQ2-4MM	4mm (0.157\"
PLPQ2-5MM	5mm (0.197\"
PLPQ2-6MM	6mm (0.236\"
PLPQ2-7MM	7mm (0.276\"
PLPQ2-8MM	8mm (0.315\"
PLPQ2-9MM	9mm (0.354\"
PLPQ2-10MM	10mm (0.394\"

CUSTOMER USE DRAWING


STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: SQUARE LIGHT PIPE, LOW PROFILE, 2mm, FRONT MOUNT	
.XX ± .01			
.XXX ± .005			
DESIGNED: M. DOAN	DATE: 07/26/12	DRAWING NO: PLPQ2-XXX	
REVISED: K. BARON	DATE: 07/24/26	SHEET SIZE A	CAGE CODE: 32559
CHECKED: A. VALDEZ	DATE: 07/24/26	SCALE: N/A	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

2. MATERIAL: POLYCARBONATE, 94V-0, CLEAR

1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101 and BSMC-1001.

OTHER AVAILABLE COLORS
* SEE TABLE FOR ORDERING INFORMATION

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		



COLOR	Order Code
BLUE	BE
BLACK	BK
GREEN	GN
RED	RD
YELLOW	YW

NOTE: LEAVE ORDER CODE BLANK
IF NO COLOR IS DESIRED.

CUSTOMER USE DRAWING

3. PARTS ARE DYED TO COLOR UPON REQUEST.

BIVAR			
CAGE CODE:	32559	PART NO: PLPQ2-XXX	REVISION: C
SHEET SIZE:	A	SCALE: 1:1	SHEET # 2 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			