







DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012

TO


MATED (2:1)



3> PACKAGING CONDITION(FREE)



RECOMMEND PCB LAYOUT (CONNECTOR MOUNTING SURFACE)



NOTES

- 1> A CIRCUIT OF COAXIAL CONNECTOR IS AS PER BELOW.
DISCONNECTED
PLUG CIRCUIT RECEPTACLE CIRCUIT
CONNECTED
- 2> COAXIAL AND CONTACT COPLANARITIES ARE 0.1 MAX.
DIMENSION OF CONTACT LEAD POSITION IS -0.15 TO 0.
- 3> ONE REEL CONTAINS 1000 PIECES IN 32mm WIDHTAPE
AND REEL PACKAGING.

5	COPPER ALLOY	CONTACT PORTION : GOLD PLATING 0.3μm MIN. SOLDERING PORTION : GOLD PLATING 0.03μm MIN.			
4	COPPER ALLOY	CONTACT PORTION : GOLD PLATING 0.3μm MIN. SOLDERING PORTION : GOLD PLATING 0.03μm MIN.	10	STAINLESS STEEL	
3	STAINLESS STEEL	TIN REFLOW PLATING 1μm MIN.	9	STAINLESS STEEL	
2	COPPER ALLOY	CONTACT PORTION : GOLD PLATING 0.3μm MIN. SOLDERING PORTION : GOLD PLATING 0.03μm MIN.	8	STAINLESS STEEL	TIN PLATING 1μm MIN.
1	POLYAMIDE(9T)	(BLACK) UL94V-0	7	STAINLESS STEEL	
			6	COPPER ALLOY	CONTACT PORTION : GOLD PLATING 0.3μm MIN. SOLDERING PORTION : GOLD PLATING 0.03μm MIN.
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED
			<i>K. Naganuma</i> '06.05.19	<i>K. Naganuma</i> '06.05.19	<i>N. Miyazaki</i> '06.05.19
			<i>Shioyuki</i> '06.05.19		
DRAWING NO. EDC3-125738-01			PART NO. MQ/S198A-10P(11)		
SCALE 4 : 1			CODE NO. CL206-2523-4-11		
UNITS mm			1/1		
HRS HIROSE ELECTRIC CO., LTD					