



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	APPROVED FOR PRODUCTION	05/04/01	MCCORMICK
B	REVISED PICTORALLY ONLY	11/26/01	MCCORMICK
C	REVISED TOLERANCES (ECN 1489)	08/08/03	MCCORMICK
D	ECN 3124: UPDATE DWG FORMAT	12/19/07	D.GRIFFIN



BNC PLUG



2X BNC JACK



CIRCUIT DIAGRAM

SPECIFICATIONS;

MATERIALS;
SHELL: BRASS
CONTACTS: BRASS
INSULATOR: DELRIN

FINISH;
SHELL: NICKEL
CONTACT: GOLD

ELECTRICAL;
CHARACTERISTIC IMPEDANCE: 50 OHMS

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] .XX ±.01 [.25] .XXX ±.005 [.13] ANGLES ±2° OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / - 0 > 60 [1524] +5% / -0%	APPROVALS	DATE	L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	05/04/2001	CATEGORY COAXIAL		PRODUCT DESCRIPTION TEE ADAPTOR BNC M/F/F	
	CHECKED BY D.PARHAM	05/04/2001	SIZE A		FSCM NO. 43321	DWG. NO. BA250
	APPROVED BY R.CARRICK	05/04/2001	SCALE: NONE		CAD FILE: BA250.SLDDRW	SHEET 1 OF 1
PROJ 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		REV. D			