


**Data Sheet | Item Number: 216-208**

Ferrule; Sleeve for 6 mm<sup>2</sup> / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow

<https://www.wago.com/216-208>



Color: ■ yellow



Dimensions in mm

| Connection Data                     |                                     |
|-------------------------------------|-------------------------------------|
| Metric cross-section of the ferrule | 6 mm <sup>2</sup>                   |
| Strip length                        | 14 ... 15 mm / 0.55 ... 0.59 inches |
| Cross-section (AWG) of ferrule      | 10 AWG                              |

| Physical data                         |        |
|---------------------------------------|--------|
| Total length (L)                      | 20 mm  |
| Wall thickness of crimp sleeve (W2)   | 0.2 mm |
| Wall thickness (plastic collar W1)    | 0.3 mm |
| Crimp length (length of sleeve L1)    | 12 mm  |
| Inner diameter of plastic collar (D1) | 6.3 mm |
| Diameter crimp sleeve inside (D2)     | 3.5 mm |

| Mechanical data |                 |
|-----------------|-----------------|
| Plastic collar  | Standard collar |
| Suitable        | 2006 Series     |

| Material data |          |
|---------------|----------|
| Color         | yellow   |
| Fire load     | 0.004 MJ |
| Weight        | 0.4 g    |

| Commercial data       |                                |
|-----------------------|--------------------------------|
| Product Group         | 2 (Terminal Block Accessories) |
| PU (SPU)              | 1000 (100) pcs                 |
| Packaging type        | Box                            |
| Country of origin     | DE                             |
| GTIN                  | 4017332277532                  |
| Customs tariff number | 85369010000                    |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 39121405             |
| eCl@ss 10.0            | 27-40-02-01          |
| eCl@ss 9.0             | 27-40-02-01          |
| ETIM 9.0               | EC000005             |
| ETIM 10.0              | EC000005             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 216-208

↓

| Documentation |            |                 |   |
|---------------|------------|-----------------|---|
| Bid Text      |            |                 |   |
| 216-208       | 19.02.2019 | xml<br>2.80 KB  | ↓ |
| 216-208       | 11.09.2017 | doc<br>24.50 KB | ↓ |

CAD/CAE-Data


CAD data

2D/3D Models 216-208

↓



Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable