

Miniature Slide Switches


Specifications:

Contact rating:	30 V DC, 350 mA
Contact resistance:	< 20 mΩ
Insulation resistance:	> 100 MΩ at 500 V DC
Dielectric strength:	500 V, 50 Hz for the duration of 1 minute
Operating temperature:	– 10 °C to + 85 °C
Mechanical life:	minimum 10 000 operations
Contacts:	copper alloy, silver-plated over nickel barrier
Contact timing:	shorting (non-shorting only if specified)
Slide colour:	black, further colours on request
Soldering conditions:	wave-soldering – max.: 5 sec, 260 °C ± 5 °C


6

Models:	Operating positions		Length (mm)	
			A	B


MFP 1220	2		13.0	7.5
MFP 1320	3		15.5	10.0
MFP 1620	6		23.0	17.5



MFP 1220 – R	2		13.0	7.5
MFP 1320 – R	3		15.5	10.0



MFP 1323	3		15.5	10.2
MFP 1424	4		18.0	12.5



MFP 1323 – R	3		15.5	10.1
--------------	---	--	------	------

