




B





PLUG HOUSING
SCALE 2.5



PLUG BODY




CONTACTS (8)



WIRE GUIDE
SURFACES

- NOTES:
- 1- PART CONSISTS OF:
PRE-INSERTED PLUG BODY
 - 2- MATERIALS:
FRONT HOUSING PLASTIC : CLEAR POLYCARBONATE, UL 94-V0
CONTACTS : PHOSPHOR BRONZE, SELECTIVE GOLD PLATING
 - 3- CONTACTS TERMINATE SOLID OR STRANDED CONDUCTORS BETWEEN
.042 [1.07] TO .048 [1.22] OUTSIDE DIAMETER OF INSULATION
 - 4- DESIGNED FOR CATEGORY 5/5e APPLICATIONS.
 - 5- DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
 - 6- TERMINATED PLUG HEIGHT: .237 [6.02] $\pm$.005 [0.13]
 7. FOR PRODUCT SPECIFICATION SEE PR026-01.

A





GENERAL VIEWS

RoHS



BULK	50 MICRO-INCHES [1.27um]	SS-37000-009
PACKAGE	CONTACT PLATING IN MATING AREA	PART NUMBER

THIRD ANGLE PROJECTION				stewart CONNECTOR a bel group		11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512 http://www.stewartconnector.com	
							
DO NOT SCALE DRAWING		UNSHIELDED CAT 5 PLUG					
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE							
DIMENSIONS: INCHES [METRIC]		THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/				DRN BY:	DATE
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE $\pm .005$ [0.13] ANGLES ARE $\pm 1^\circ$						TRM	6-29-06
SHEET NO.						APPD BY:	DATE
1 OF 1		DHG	6-29-06			DWG. NO.	REV.
						CT370059	B3

DATE	REV.	ECN	APP'D BY
2-17-15	B2	10258	ADB
3-1-16	B3	10578	TRM

B

A