


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/22/08	D.GRIFFIN
B	ECN 3677: DELETED NOTE 1	11/14/08	D.CASTRO
C	ECN5151: UPDATED FORMAT. CHANGED LENGTH DIM LOCATION.	11/17/10	DFP
D	ECN 5268: ADDED LABEL WITH L-COM P/N TO NOTE 2	1/21/11	D. CASTRO

"J1"
SERIAL ATA RECEPTACLE,
7 PIN CONNECTOR,
STRAIGHT, W/ LATCH,
OVERMOLDED, COLOR: BLACK

"J2"
SERIAL ATA RECEPTACLE,
7 PIN CONNECTOR,
RIGHT ANGLE, W/ LATCH,
OVERMOLDED, COLOR: BLACK


CABLE: UL21149 SERIAL ATA 26 AWG,
JACKET: PVC, COLOR: RED



PART #	LENGTH	
	INCHES	MILLIMETERS
CASATARL-8	8	203.2
CASATARL-12	12	304.8
CASATARL-16	16	406.4
CASATARL-18	18	457.2
CASATARL-24	24	609.6
CASATARL-36	36	914.4

- NOTE:**
1. EACH CABLE ASSEMBLY SHALL BE SUBJECTED TO A CONTINUITY TEST.
 2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG AND LABELED WITH L-COM PART NUMBER.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY E. STAUBLE	7/17/08		
	CHECKED BY D. PARHAM	7/21/08	CATEGORY DATA CABLING	
	APPROVED BY S. SMITH	7/21/08	PRODUCT DESCRIPTION CBL,SATA W/LATCH STR/RA	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. CASATARL-X	REV. D	
SCALE: NONE		CAD FILE: CASATARL-X.SLDDRW	SHEET 1 OF 1	