

D-SUB M 3W3 FE TH



Image is for illustration purposes only. Please refer to product description.

Part number	09 69 200 0033
Specification	D-SUB M 3W3 FE TH
HARTING eCatalogue	https://harting.com/09692000033

Identification

Category	Connectors
Series	D-Sub
Identification	Mixed
Element	Connector
Description of the contact	Straight

Version

Gender	Female
Size	D-Sub 2
Number of contacts	3
Number of signal contacts	0
Number of special contacts	3x
Locking type	Fixing flange with feed through hole Ø 3.1 mm
Details	Please order special contacts separately.

Technical characteristics

Insulation resistance	$> 5 \times 10^9 \Omega$
Limiting temperature	-55 ... +125 °C
Mating cycles	≥ 500
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ($175 \leq CTI < 400$)
Hot plugging	No



Pushing Performance
Since 1945

Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (Polyester) Shell: steel, tin plated
Colour (insert)	Green
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
----------	-----------------------

Commercial data

Packaging size	100
Net weight	7.06 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140097346
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136
UNSPSC 24.0	39121469